

AGB**P1****JH2**

AFOCUS ANIMATIC	(5)RX	n	JH2-1	BLU
	TX	U	JH2-2	WHT
	GND	T	JH2-3	YEL
		AA	JH2-4	
	48V	z	JH2-5	GRN
	GND	m	JH2-6	BLK
	48V	k	JH2-7	GRN
	GND	S	JH2-8	BLK
	48V	GG	JH2-9	GRN
	GND	j	JH2-10	BLK
CAMERA ANIMATIC	(4)RX	P	JH2-11	BRN
	TX	R	JH2-12	WHT
	GND	i	JH2-13	YEL
		y	JH2-14	
	48V	N	JH2-15	ORG
	GND	h	JH2-16	BLK
	48V	x	JH2-17	ORG
	GND	FF	JH2-18	BLK
	48V	M	JH2-19	ORG
	GND	g	JH2-20	BLK
		L	JH2-21	
		w	JH2-22	
		f	JH2-23	
		K	JH2-24	
		v	JH2-25	
		e	JH2-26	
		EE	JH2-27	
		HH	JH2-28	
		⊗	JH2-29	
		⊗	JH2-30	

JH1

VFOCUS ANIMATIC	(6)RX	p	JH1-1	GRN
	TX	BB	JH1-2	RED
	GND	q	JH1-3	YEL
		V	JH1-4	
	48V	A	JH1-5	RED
	GND	W	JH1-6	BLK
	48V	X	JH1-7	RED
	GND	B	JH1-8	BLK
	48V	Y	JH1-9	RED
	GND	C	JH1-10	BLK
COLLINS CCD & SHUTTR	+LED	CC	JH1-11	RED
	3V	r	JH1-12	YEL
	6V RTN	Z	JH1-13	WHT
	3V RTN	D	JH1-14	BLU
	6V	E	JH1-15	BRN
	-LED	s	JH1-16	VIO
	12V	F	JH1-17	ORG
	12V RTN	a	JH1-18	GRY
	SHTTR +	b	JH1-19	GRN
	SHTTR -	t	JH1-20	BLK
FILTER WHEEL	GND	G	JH1-21	BLK
	14VDC	c	JH1-22	BRN
	BCD1	u	JH1-23	RED
	BCD2	DD	JH1-24	ORG
	BCD4	d	JH1-25	YEL
	MTR ENABLE	H	JH1-26	BLU
	BCD8	⊗	JH1-27	GRN
	MTR ON	J	JH1-28	VIO
	SPARE	⊗	JH1-29	GRY
		J	JH1-30	

AUX

P1

JH2

AFOCUS ANIMATIC	(5)TX	n	JH2-1	RED
	RX	U	JH2-2	GRN
	GND	T	JH2-3	YEL
		AA	JH2-4	
	48V	z	JH2-5	RED
	GND	m	JH2-6	BLK
	48V	k	JH2-7	RED
	GND	S	JH2-8	BLK
	48V	GG	JH2-9	RED
	GND	j	JH2-10	BLK
CAMERA ANIMATIC	(4)TX	P	JH2-11	RED
	RX	R	JH2-12	GRN
	GND	i	JH2-13	YEL
		y	JH2-14	
	48V	N	JH2-15	RED
	GND	h	JH2-16	BLK
	48V	x	JH2-17	RED
	GND	FF	JH2-18	BLK
	48V	M	JH2-19	RED
	GND	g	JH2-20	BLK
		L	JH2-21	
		w	JH2-22	
		f	JH2-23	
		K	JH2-24	
		v	JH2-25	
		e	JH2-26	
		EE	JH2-27	
		HH	JH2-28	
		X	JH2-29	
		X	JH2-30	

JH1

VFOCUS ANIMATIC	(6)TX	p	JH1-1	RED
	RX	BB	JH1-2	GRN
	GND	q	JH1-3	YEL
		V	JH1-4	
	48V	A	JH1-5	RED
	GND	W	JH1-6	BLK
	48V	X	JH1-7	RED
	GND	B	JH1-8	BLK
	48V	Y	JH1-9	RED
	GND	C	JH1-10	BLK
COLLINS CCD	+LED	CC	JH1-11	ORG
	3V	r	JH1-12	BLU
	6V RTN	Z	JH1-13	BLK
	3V RTN	D	JH1-14	WHT
	6V	E	JH1-15	RED
	-LED	s	JH1-16	GRN
	12V	F	JH1-17	VIO
	12V RTN	a	JH1-18	GRY
SHUTTR	+	b	JH1-19	GRN
	-	t	JH1-20	BLK
FILTER WHEEL	GND	G	JH1-21	BLK
	14VDC	c	JH1-22	BRN
	BCD1	u	JH1-23	RED
	BCD2	DD	JH1-24	ORG
	BCD4	d	JH1-25	YEL
	MTR ENABLE	H	JH1-26	BLU
	BCD8	X	JH1-27	GRN
	MTR ON	J	JH1-28	VIO
	SPARE	X	JH1-29	GRY
		J	JH1-30	

<u>RACK #1 (MAX 16U/28 IN.)</u>	<u>U</u>	<u>HT (IN.)</u>
PI TIP TILT	3	5.25
NEWPORT ACTUATOR BOX	3	5.25
AO VME CHASSIS	6	10.50
WFS UTIL BOX	3	5.25
SORENSEN PWR SUPPLY	1	1.75

<u>RACK #2 (MAX 11U/19.25 IN.)</u>		
RELAY UTIL BOX	3	5.25
ACQUISITION UTIL BOX	4	7.00
BAYTECH A/C PWR CNTLR	1	1.75
SPARE	3	5.25